

Push Buttons – 800P and 800T



Palm Button Station

This complete palm button station includes a black push button boot, die cast gray guard, and legend plate. This preferred configuration uses a boot for applications where the standard silver button may be slippery.

And the legend plate addition offers clear function indication.

Configuration

- 800P surface mount with articulated chrome palm button, die cast gray guard, black boot and START legend plate. Includes 1 N.O. and 1 N.C. contact block and base with double hub

Catalog Number

800P-NX11

30mm Illuminated E-Stop Operator with Legend Cap

This complete 30mm E-Stop button offers clear indication with E-STOP text printed on the illuminated mushroom cap.



Configuration

- 30mm illuminated E-Stop with a legend text cap "E-Stop" and 1 N.C.L.B. and 1 N.O. contact block

Catalog Number

800T-NX1487



30mm Flush and Extended Momentary Push Buttons with Blank Cap

These 30mm flush and extended operators are configured for applications that can benefit from caps without the A-B logo.

Configuration

- The "P" option is for the blank cap. The "x" option is for the color cap and the "yy" option is for the contact blocks

Example:

800T Momentary Flush Push Button with black blank cap and 1 N.O. and 1 N.C. contact block

Catalog Number

800T-AxPyy

800T-A2PA

30mm Locking Push Button with Guarded Bezel

This is a 30mm locking push button that comes with a guarded bezel to prevent accidental activation.



Configuration

- 30mm locking push button with two 1 N.O. contact blocks and a guarded bezel

Catalog Number

800T-NX970