








Limit Switches

Operating Levers

For use with 802T, 802M, 802MC, 802X, 802XR





Rod Levers

Type	Material	Dia.	Cat. No.
	Stainless Steel Rod 5" Long	0.13"	802T-W3②
	Stainless Steel Rod 8.5" Long	0.13"	802T-W3B②
	Stainless Steel Rod 12" Long	0.13"	802T-NX50
	Stainless Steel Rod 11.5" Long	0.13"	802T-W3A
	Stainless Steel Rod 14" Long	0.08"	802T-W3F②
	Nylon Rod 12" Long	0.25"	802T-W3C 802T-NX142 ⑤
	Stainless Steel Rod 5" Long	0.06"	802T-W5②
	Stainless Steel Rod 5" Long	0.06"	802T-W5②
	Stainless Steel Rod 5" Long One-Way	0.06"	802T-W8①
	Nylatron Looped Rod 6" Long 2" Wide Loop	0.18"	802T-W14
	Nylatron Looped Rod 9" Long 2" Wide Loop	0.18"	802T-NX119
	Steel Rod 9" Long	0.25"	802T-W16
	Nylon Rod 9" Long	0.25"	802T-W16A

Approximate Dimensions—See page 5-133.


- ① Do not use on maintained contact limit switches.
- ② Recommended for use with low operating torque switches.
- ③ Not for use with 802M-NPY5 or 802M-ASY5 type switches.
- ④ TUFGRAM® is a synergistic coating which combines the advantages of anodizing with a controlled infusion of PTFE for added corrosion resistance.
- ⑤ Recommended for high impact applications.

Rod Levers—Corrosion-Resistant


Type	Material	Dia.	Cat. No.
	Type 316 stainless steel rod 5" long Block is cast aluminum protected with TUFGRAM®④	0.13"	802MC-W3
	Type 316 stainless steel rod 11.5" long Block is cast aluminum protected with TUFGRAM®④	0.08"	802MC-W3A
	Nylon Rod 12" long Block is cast aluminum protected with TUFGRAM®④	0.25"	802MC-W3C
	Nylon Rod Only	0.25"	WF25507

Operating Levers


Approximate Dimensions [mm (in.)] (continued)




802T-W4A and 802T-W4C
Shipping Wt. 57g (2oz)




802T-W4F
Shipping Wt. 57g (2oz)




802T-W5
Shipping Wt. 28g (1oz)




802T-W6, 802T-W6A,
802T-W6B, 802T-W6E
Shipping Wt. 57g (2oz)




802T-W6F
Shipping Wt. 57g (2oz)




802T-W7, 802T-W7A
and 802T-W7B
Shipping Wt. 57g (2oz)




802T-W8
Shipping Wt. 43g (1.5oz)




802T-W9
Shipping Wt. 28g (1oz)




802T-W12 Shipping Wt. 1 oz. and
802T-W12A 802T-W6B, 802T-W6E
Shipping Wt. 43g (1.5oz)




802T-W14
Shipping Wt. 43g (1.5oz)



802T-W16
802T-W16A



802T-W20
Shipping Wt. 57g (2oz)



802T-W20J
Shipping Wt. 57g (2oz)