

Product: 855H-BA10BD

Description: 855H High Performance Electronic Horns



Representative Photo Only
(actual product may vary based
on configuration selections)

HORN DATA

Voltage

115V AC 50/60Hz

Horn Type

104 dB / 32 tone gray

Mounting Option

Standard Base - Back feed or conduit feed

CERTIFICATIONS AND APPROVALS

cULus

Listed, Guide No. UCST, File No. S6583

CE

Marked

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>