

Product: 855H-BCD24ADR5

Description: 855H High Performance Electronic Horns with Beacon



Representative Photo Only
(actual product may vary based
on configuration selections)

HORN DATA

Voltage	24V DC
Horn Type	100 dB / 10 tone gray
Mounting Option	Standard Base - Back feed or conduit feed

BEACON DATA

Illumination Type	5 Joule Strobe
Lens Color	Amber

CERTIFICATIONS AND APPROVALS

cULus	Listed, Guide No. UCST, File No. S6583
CE	Marked
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm