

**Product:** 855H-BCD24BDR5

**Description:** 855H High Performance Electronic Horns with Beacon



Representative Photo Only  
(actual product may vary based  
on configuration selections)

#### HORN DATA

Voltage	24V DC
Horn Type	104 dB / 32 tone gray
Mounting Option	Standard Base - Back feed or conduit feed

#### BEACON DATA

Illumination Type	5 Joule Strobe
Lens Color	Amber

#### CERTIFICATIONS AND APPROVALS

cULus	Listed, Guide No. UCST, File No. S6583
CE	Marked
For UL Certifications Directory:	<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>