

Product: 855XM-CGMD24DA4
Description: 855XM Hazardous Location Metal Horns



Representative Photo
Only (actual product
may vary based on
configuration
selections)

METAL HORN SELECTION

Type	Horn with Beacon
Housing Color	Gray
Conduit Entry	M20 x 1.5mm Conduit Entry
Voltage	20-28V DC
Output	116dB Output
Beacon Type	5J Strobe
Lens Color	Red