

Main Page		Company Profile		Employment		What's New		Contact Us	
								ALLIED MOULDED PRODUCTS, Inc Residential Products	
>> Residential Home : Choose a Category Below									
Contractor Testimonial - Residential Outlet Boxes		2302-NKV		Request a Catalog		Find a Sales Rep		Find a Stocking Distributor	
Inspector Information						Two gang, angled mid-nails, Speed Klamps™			
Fiberglassbox™ Switch and Outlet Boxes						Volume (Cu. In.): 37.0 Depth (In.): 3 7/16 Width (In.): 4 Height (In.): 3 3/4			
Fiberglassbox™ Old Work Outlet Boxes		Standard Quantity: 48 Standard Weight (Lbs.): 33 UPC: 8533913077				Material: Thermoset-Fiberglass			
Vapor Seal/Air-Sealed Type Boxes		Test Spec: UL® Listed per UL® 514 C				Fire Rating Classification: 2-HR Wall			
SLIDERBOX® Adjustable Outlet Boxes		Made in the U.S.A.							
Flexbox® Switch and Outlet Boxes									
Flexbox® Old Work Outlet Boxes									
Specialty Products									
Speed "K" Klamps™									
Request a Catalog									
Your New Product Ideas									
Residential Home Brochure									
Material Safety Data Sheets									
Made In USA									
Rep Login									
Main Page Company Profile Employment Products Sitemap Contact Us Electrical Box Fan Box Outlet Box © Copyright Allied Moulded Products, Inc. 222 N. Union St., Bryan, OH 43506. Phone: 419-636-4217									