



<p> <a href="#">Main Page</a> <a href="#">Company Profile</a> <a href="#">Employment</a> <a href="#">What's New</a> <a href="#">Contact Us</a> </p>		 <p><b>ALLIED MOULDED PRODUCTS, Inc</b> Residential Products</p>	
<p>&gt;&gt; Residential Home : Choose a Category Below</p>			
<p> <a href="#">Contractor Testimonial - Residential Outlet Boxes</a>   <a href="#">Inspector Information</a>   <a href="#">Fiberglassbox™ Switch and Outlet Boxes</a>   <a href="#">Fiberglassbox™ Old Work Outlet Boxes</a>   <a href="#">Vapor Seal/Air-Sealed Type Boxes</a>   <a href="#">SLIDERBOX® Adjustable Outlet Boxes</a>   <a href="#">Flexbox® Switch and Outlet Boxes</a>   <a href="#">Flexbox® Old Work Outlet Boxes</a>   <a href="#">Specialty Products</a>   <a href="#">Speed "K" Klamps™</a>   <a href="#">Request a Catalog</a>   <a href="#">Your New Product Ideas</a>   <a href="#">Residential Home Brochure</a>   <a href="#">Material Safety Data Sheets</a>   <a href="#">Made In USA</a>   <a href="#">Rep Login</a> </p>	<p>4304-NKV</p> <p> <a href="#">Request a Catalog</a> <a href="#">Find a Sales Rep</a> <a href="#">Find a Stocking Distributor</a> </p>		<p><b>Four gang, angled mid-nails, Speed Klamps™</b></p> <p>Volume (Cu. In.): 75.0</p> <p>Depth (In.): 3 9/16 Width (In.): 7 1/2 Height (In.): 3 3/4</p> <p>Standard Quantity: 18 Standard Weight (Lbs.): 22 UPC: 8533917558</p> <p>Material: Thermoset-Fiberglass</p> <p>Test Spec: UL® Listed per UL® 514 C</p> <p>Fire Rating Classification: 2-HR Wall</p>
			
	<p>Made in the U.S.A.</p>		
	<p>Main Page   Company Profile   Employment   Products   Sitemap   Contact Us   Electrical Box   Fan Box   Outlet Box © Copyright Allied Moulded Products, Inc. 222 N. Union St., Bryan, OH 43506. Phone: 419-636-4217</p>		