

[Main Page](#)
[Company Profile](#)
[Employment](#)
[What's New](#)
[Contact Us](#)



ALLIED MOULDED PRODUCTS, Inc
Residential Products

>> Residential Home : Choose a Category Below

[Contractor Testimonial - Residential Outlet Boxes](#)

[Inspector Information](#)

[Fiberglassbox™ Switch and Outlet Boxes](#)

[Fiberglassbox™ Old Work Outlet Boxes](#)

[Vapor Seal/Air-Sealed Type Boxes](#)

[SLIDERBOX® Adjustable Outlet Boxes](#)

[Flexbox® Switch and Outlet Boxes](#)

[Flexbox® Old Work Outlet Boxes](#)

[Specialty Products](#)

[Speed "K" Klamps™](#)

[Request a Catalog](#)

[Your New Product Ideas](#)

[Residential Home Brochure](#)

[Material Safety Data Sheets](#)

[Made In USA](#)

[Rep Login](#)

9331-EWK

 [Request a Catalog](#)  [Find a Sales Rep](#)  [Find a Stocking Distributor](#)



Ears, wing brackets, Speed Klamps™

Volume (Cu. In.): 14.0

Depth (In.): 2 1/2

Width (In.): 2 3/8

Height (In.): 3 1/4

Standard Quantity: 100
Standard Weight (Lbs.): 30
UPC: 8533938511

Material: Thermoset-Fiberglass

Test Spec: UL® Listed per UL® 514 C

Fire Rating Classification: 2-HR Wall & Ceiling

Made in the U.S.A.