

[Main Page](#)[Company Profile](#)[Employment](#)[What's New](#)[Contact Us](#)

**ALLIED MOULDED PRODUCTS, Inc**  
Residential Products

>> Residential Home : Choose a Category Below

[Contractor Testimonial - Residential Outlet Boxes](#)

[Inspector Information](#)

[Fiberglassbox™ Switch and Outlet Boxes](#)

[Fiberglassbox™ Old Work Outlet Boxes](#)

[Vapor Seal/Air-Sealed Type Boxes](#)

[SLIDERBOX® Adjustable Outlet Boxes](#)

[Flexbox® Switch and Outlet Boxes](#)

[Flexbox® Old Work Outlet Boxes](#)

[Specialty Products](#)

[Speed "K" Klamps™](#)

[Request a Catalog](#)

[Your New Product Ideas](#)

[Residential Home Brochure](#)

[Material Safety Data Sheets](#)

[Made In USA](#)

[Rep Login](#)

9335-BHKV2

 [Request a Catalog](#) [Find a Sales Rep](#) [Find a Stocking Distributor](#)



**Double sheet drywall set back, "BH" 16" to 24" adjustable bar hanger, Speed Klamps™, 50 lb. fixture rated**

Volume (Cu. In.): 20.5

Depth (In.): 2 15/16  
Diameter (In.): 3 1/2

Ceiling Joist Span (In.): 16 In. and 24 In.

Standard Quantity: 18  
Standard Weight (Lbs.): 25  
UPC: 8533988125

Material:  
Thermoset-Fiberglass

Fixture Support Rating:  
50 lb.

Test Spec:  
UL® Listed per UL® 514 C

Fire Rating Classification:  
2-HR Wall & Ceiling

Rated for use in 16 Inch and 24 Inch span ceiling joist applications and meets the April 2010 UL® deflection requirements and 2008 National Electrical Code (Section 314.27A)

Made in the U.S.A.

[Main Page](#) | [Company Profile](#) | [Employment](#) | [Products](#) | [Sitemap](#) | [Contact Us](#) | [Electrical Box](#) | [Fan Box](#) | [Outlet Box](#)  
© Copyright Allied Moulded Products, Inc. 222 N. Union St., Bryan, OH 43506. Phone: 419-636-4217