

Main Page
Company Profile
Employment
What's New
Contact Us



ALLIED MOULDED PRODUCTS, Inc
Residential Products

>> Residential Home : Choose a Category Below

<p>Contractor Testimonial - Residential Outlet Boxes</p> <p>Inspector Information</p> <p>Fiberglassbox™ Switch and Outlet Boxes</p> <p>Fiberglassbox™ Old Work Outlet Boxes</p> <p>Vapor Seal/Air-Sealed Type Boxes</p> <p>SLIDERBOX® Adjustable Outlet Boxes</p> <p>Flexbox® Switch and Outlet Boxes</p> <p>Flexbox® Old Work Outlet Boxes</p> <p>Specialty Products</p> <p>Speed "K" Klamps™</p> <p>Request a Catalog</p> <p>Your New Product Ideas</p> <p>Residential Home Brochure</p> <p>Material Safety Data Sheets</p> <p>Made In USA</p> <p>Rep Login</p>	<div style="border: 1px solid black; padding: 5px; margin-bottom: 5px;"> <p>9369-FB</p> <div style="display: flex; justify-content: space-around; font-size: small;"> Request a Catalog Find a Sales Rep Find a Stocking Distributor </div> </div> <div style="display: flex; align-items: flex-start;"> <div style="flex: 1; text-align: center;">  </div> <div style="flex: 2; padding-left: 10px;"> <p>4" dia. surface mount fan and fixture box, Speed Klamps™</p> <p>Volume (Cu. In.): 16.0</p> <p>Depth (In.): 1 3/4 Width (In.): 4</p> <p>Standard Quantity: 25 Standard Weight (Lbs.): 11 UPC: 8533976500</p> <p>Material: Thermoset-Fiberglass</p> <p>Fixture Support Rating: 50 lb.</p> <p>Fan Support Rating: 35 lb.</p> <p>Test Spec: UL® Listed per UL® 514 C</p> <p>Fire Rating Classification: 2-HR Wall & Ceiling</p> </div> </div> <p style="margin-top: 10px;">Made in the U.S.A.</p>
---	---

[Main Page](#) | [Company Profile](#) | [Employment](#) | [Products](#) | [Sitemap](#) | [Contact Us](#) | [Electrical Box](#) | [Fan Box](#) | [Outlet Box](#)
 © Copyright Allied Moulded Products, Inc. 222 N. Union St., Bryan, OH 43506. Phone: 419-636-4217