



## 9350-BHGC2



VIDEO

### Product Description

4" dia. round fixture support box for use with nonmetallic sheathed cable

**Brand:** fiberglassBOX™  
**Catalog #:** 9350-BHGC2

**Carton Quantity:** 24  
**Carton Weight:** 33 lb.

**Width:** 4 in.  
**Depth:** 2-7/16 in.  
**Volume:** 22.5 cu. in.  
**Type of Installation:** New Work  
**Round Ceiling Box**

**UPC:** 085339881216  
**UNSPSC:** 39121316  
**Country of Origin:** United States of America

### FEATURES

Machine tapped fixture holes, ground strap, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures

### APPLICATION

New work residential construction 2 HR fire resistive walls and ceilings (50 lbs. fixture support)

### STANDARDS

ANSI / UL 514C: File No. E30594



### FIRE CLASSIFICATION

#### Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

*Note: Products must also be certified to: ANSI / UL 514C*

#### Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

#### Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 1/2 inches

*Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)*

### COLOR

Beige/tan

### MATERIAL

Fiberglass reinforced polyester BMC

### MOUNTING

Adjustable bar hanger - 16" to 24" on center joist application

### ADDITIONAL MATERIALS

Galvanized steel brackets and plated carbon steel fasteners

Plated carbon steel clamp and fasteners

Galvanized ground strap with plated carbon steel fastener and green plated carbon steel ground screw

### SUPPORT RATING

50 lbs fixture support