



## 9336-NKFR



VIDEO

### Product Description

3.5" dia. round fan support box for use with nonmetallic sheathed cable

**Brand:** fiberglassBOX™  
**Catalog #:** 9336-NKFR

**Carton Quantity:** 50  
**Carton Weight:** 23 lb.

**Width:** 3-1/2 in.  
**Depth:** 2-3/8 in.  
**Volume:** 16 cu. in.  
**Type of Installation:** New Work  
**Round Ceiling Box**

**UPC:** 085339103059  
**UNSPSC:** 39121316  
**Country of Origin:** United States of America

### FEATURES

Machine tapped fixture holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps factory installed

### APPLICATION

New work residential construction 2 HR fire resistive walls and ceilings (35 lbs. fan support and 50 lbs. fixture support)

### STANDARDS

ANSI / UL 514C: File No. E30594



### FIRE CLASSIFICATION

#### Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

*Note: Products must also be certified to: ANSI / UL 514C*

#### Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

#### Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 1/2 inches

*Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)*

### COLOR

Beige/tan

### MATERIAL

Fiberglass reinforced polyester BMC

### MOUNTING

Nail-on with fetter ring nails

### ADDITIONAL MATERIALS

Carbon steel fasteners

Polyvinyl chloride clamps

### SUPPORT RATING

50 lbs fixture support and 35 lbs fan support