



AC9500



Product Description

4" dia. round fixture support box with 7" square mounting flange for use with nonmetallic sheathed cable

Brand: fiberglassBOX™
Catalog #: AC9500

Width: 4 in.
Depth: 1-1/4 in.
Volume: 12 cu. in.
Type of Installation: New Work
Wall Box

Carton Quantity: 20
Carton Weight: 12 lb.

UPC: 085339095002
UNSPSC: 39121309
Country of Origin: United States of America

FEATURES

Machine tapped fixture holes, "pop-in" cable clamp, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures

APPLICATION

Residential home - exterior light fixture electrical box (15 lb fixture rating) for use with nonmetallic sheathed cable

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 24 inches

Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes must be 4-1/2 feet from one another

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Beige/tan

ADDITIONAL MATERIALS

Nonmetallic pop-in cable clamp

MATERIAL

Fiberglass reinforced polyester BMC

SUPPORT RATING

15 lb fixture support

MOUNTING

Back side mount with fasteners