



## 9342-C2



VIDEO

### Product Description

4 square inch electrical junction box for use with nonmetallic sheathed cable

**Brand:** fiberglassBOX™  
**Catalog #:** 9342-C2

**Height:** 4 in.  
**Width:** 4 in.  
**Depth:** 2-1/4 in.  
**Volume:** 27.3 cu. in.  
**Type of Installation:** New Work  
**Wall Box**

**Carton Quantity:** 50  
**Carton Weight:** 25 lb.

**UPC:** 085339103462  
**UNSPSC:** 39121332  
**Country of Origin:** United States of America

### FEATURES

Machine tapped cover screw holes, cover screws included, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures

### APPLICATION

In the wall junction box with optional single and two gang plaster ring covers for junction box capacity and device applications - 2 HR fire resistive walls

### STANDARDS

ANSI / UL 514C: File No. E30594



### FIRE CLASSIFICATION

#### Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

#### Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

### COLOR

Beige/tan

### ADDITIONAL MATERIALS

Plated carbon steel clamp and fasteners

### MATERIAL

Fiberglass reinforced polyester BMC

Carbon steel fasteners

### MOUNTING

Bottom mount