



# AMU664CCHF



VIDEO

## Product Description

Wall mount enclosure assembly

**Cover Type:** Hinged 2-Screw Clear Cover

**Brand:** ULTRALINE®  
**Catalog #:** AMU664CCHF

**Height:** 6.04 in.  
**Width:** 6.26 in.  
**Depth:** 3.99 in.  
**Usable Depth:** 4.09 in.  
**Volume:** 190 cu. in.

**Carton Quantity:** 1  
**Carton Weight:** 3 lb.

**UPC:** 085339958185  
**UNSPSC:** 39121324

**Patents:**  
U.S. Patent No. 7,572,975  
**Country of Origin:** United States of America

## FEATURES

Non-corrosive, non-conductive, light weight with lower installation cost, easy to modify and longer life cycle compared to steel. Rigid design with back panel inserts plus nonmetallic mounting brackets and a gasket system encased in a continuous channel on the cover.

## APPLICATION

Enclose and protect electrical and electronic controls, instruments or components for indoor and outdoor applications. Especially well suited for extreme temperature and corrosive environments.

## STANDARDS

UL 508A, UL 50 and UL 50E Types 1, 2, 3, 3R, 4, 4X, 12 and 13; File No. E120175

CSA-C22.2 No. 14 and CSA C22.2 No. 94 Types 1, 2, 3, 3R, 4, 4X, 12 and 13; File No. 89590

Complies with:

1. EN / IEC 60204-1 and 60529 Type IP66
2. RoHS directive



## COLOR

RAL 7035 - Gray with clear cover

## ENCLOSURE ACCESSORIES

Back Panels, Hinged Front Panel, Hole Plugs, Vent Kits, and Pole Mount Kit

## MATERIAL

ULTRAGUARD® Fiberglass reinforced polyester - compression molded SMC box and clear polycarbonate cover

## ADDITIONAL MATERIALS

316 stainless steel external hardware (hinges, latches and fasteners)

Polycarbonate mounting brackets

Plated carbon steel internal hardware

## MOUNTING

Nonmetal flange fastened to back side brass insert

Brass inserts

Polyurethane (FIP) Formed-In-Place gasket system