



## PC213-16



### Product Description

3.5" dia. round fixture support box for use with nonmetallic sheathed cable

**Brand:** flexBOX®  
**Catalog #:** PC213-16

**Carton Quantity:** 24  
**Carton Weight:** 17 lb.

**Width:** 3-1/2 in.  
**Depth:** 2-13/16 in.  
**Volume:** 21 cu. in.  
**Type of Installation:** New Work  
**Round Ceiling Box**

**UPC:** 085339983040  
**UNSPSC:** 39121316  
**Patents:**  
U.S. Patent No. 6,365,831 B1  
**Country of Origin:** United States of America

### FEATURES

Machine tapped fixture holes

### APPLICATION

New work residential construction 2 HR fire resistive walls and ceilings (50 lbs. fixture support)

### STANDARDS

ANSI / UL 514C: File No. E30594



### FIRE CLASSIFICATION

#### Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

*Note: Products must also be certified to: ANSI / UL 514C*

#### Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 1/2 inches

*Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)*

### COLOR

Black

### ADDITIONAL MATERIALS

Galvanized steel brackets and plated carbon steel fasteners

### MATERIAL

Polycarbonate

### SUPPORT RATING

50 lbs fixture support

### MOUNTING

Adjustable bar hanger - max 16" on center Joist application