



9318



VIDEO

Product Description

Single gang electrical box for use with nonmetallic sheathed cable

Brand: fiberglassBOX™
Catalog #: 9318

Height: 4-3/16 in.
Width: 2-1/4 in.
Depth: 2 in.
Volume: 12.5 cu. in.
Wall Box
Number of Gangs: 1

Carton Quantity: 100
Carton Weight: 28 lb.

UPC: 085339101406
UNSPSC: 39121308
Country of Origin: United States of America

FEATURES

Machine tapped device holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures

APPLICATION

Surface mounted box with side and bottom romex cable openings

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 ½ inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Beige/tan

MATERIAL

Fiberglass reinforced polyester BMC

MOUNTING

Surface mount