



9331-EWC2



VIDEO

Product Description

Single gang electrical box for use with nonmetallic sheathed cable

Brand: fiberglassBOX™
Catalog #: 9331-EWC2

Carton Quantity: 100
Carton Weight: 33 lb.

Height: 3-1/4 in.
Width: 2-3/8 in.
Depth: 2-1/2 in.
Volume: 14 cu. in.
Type of Installation: Old Work
Wall Box
Number of Gangs: 1

UPC: 085339385103
UNSPSC: 39121308
Country of Origin: United States of America

FEATURES

Machine tapped device holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures

APPLICATION

Old work residential construction 2 HR fire resistive walls and ceilings

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 1/2 inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Beige/tan

MATERIAL

Fiberglass reinforced polyester BMC

MOUNTING

Metal wing brackets/metal ears wall compression

ADDITIONAL MATERIALS

Galvanized steel brackets and plated carbon steel fasteners

Plated carbon steel clamp and fasteners