



9339-Z+1C2



VIDEO

Product Description

4 square inch electrical junction box for use with nonmetallic sheathed cable

Brand: fiberglassBOX™
Catalog #: 9339-Z+1C2

Carton Quantity: 50
Carton Weight: 23 lb.

Height: 4-1/4 in.
Width: 4-1/4 in.
Depth: 1-1/4 in.
Volume: 16 cu. in.
Type of Installation: New Work
Wall Box

UPC: 085339103189
UNSPSC: 39121332
Country of Origin: United States of America

FEATURES

Machine tapped cover screw holes, cover screws included, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures

APPLICATION

In the wall junction box with optional single and two gang plaster ring covers for junction box capacity and device applications - 2 HR fire resistive walls

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Beige/tan

ADDITIONAL MATERIALS

Galvanized steel brackets and plated carbon steel fasteners

MATERIAL

Fiberglass reinforced polyester BMC

Plated carbon steel clamp and fasteners

Carbon steel fasteners

MOUNTING

Stud mount "Z" hanger bracket offset for flush mount plaster ring