



AM2068TW



Product Description

Wall mount enclosure assembly

Cover Type: Twist Latch Hinged Window Cover

Brand: AM Series JIC Sizes

Catalog #: AM2068TW

Height: 20 in.

Width: 16 in.

Depth: 8.01 in.

Usable Depth: 7.58 in.

Volume: 2602 cu. in.

Carton Quantity: 1

Carton Weight: 18 lb.

UPC: 085339920700

UNSPSC: 39121324

Country of Origin: United States of America

FEATURES

Non-corrosive, non-conductive, light weight with lower installation cost, easy to modify and longer life cycle compared to steel. Rigid design with back panel inserts plus stainless steel mounting brackets and a gasket system encased in a continuous channel on the cover.

APPLICATION

Enclose and protect electrical and electronic controls, instruments or components for indoor and outdoor applications. Especially well suited for extreme temperature and corrosive environments.

STANDARDS

UL 508A, UL 50 and UL 50E Types 1, 2, 3, 3R, 4, 4X, 12 and 13; File No. E120175

CSA-C22.2 No. 14 and CSA C22.2 No. 94 Types 1, 2, 3, 3R, 4, 4X, 12 and 13; File No. 89590

Complies with:

1. EN / IEC 60204-1 and 60529 Type IP66
2. RoHS directive



COLOR

RAL 7035 - Gray with clear window

MATERIAL

ULTRAGUARD® Fiberglass reinforced polyester - compression molded SMC box and cover with bonded clear polycarbonate window

MOUNTING

Stainless steel feet fastened to back side brass inserts

ENCLOSURE ACCESSORIES

Back panels, hinged-front panels, thermal management, pole mount kits, and hole plug assemblies.

ADDITIONAL MATERIALS

316 stainless steel external hardware (hinges, latches and fasteners)

316 stainless steel mounting brackets

Plated carbon steel internal hardware

Brass inserts

Polyurethane (FIP) Formed-In-Place gasket system