



## AMHS050-GY



VIDEO

### Product Description

NEMA 4X Enclosure Hole Plug Assembly

**Brand:** ULTRAPLUG®  
**Catalog #:** AMHS050-GY

**Trade Size Ref:** 1/2" Conduit (.875) nom. in.  
22mm PB (.886)

**Plugged Hole Dia. Range:** .812-.937 in.

**Plug Diameter:** 1.245 in.

**Plug Head Height:** 0.235 in.

**Nut Height:** 0.5 in.

**Carton Quantity:** 1

**Carton Weight:** 0.022 lb.

**UPC:** 085339996200

**UNSPSC:** 39121321

**Patents:**

U.S. Patent No. 9,045,932

**Country of Origin:** United States of America

### FEATURES

Plug fins are self centering, anti-rotational design for fast and easy one person assembly and no-tools tightening

### APPLICATION

Capable of plugging unused holes in NEMA 4X enclosures and designed to maintain applicable NEMA/UL/CSA enclosure ratings

### STANDARDS

Meets Requirements: ANSI/UL50, ANSI/UL50E, and ANSI/UL508A; File No. E487574

UL® listed and recognized component for use with CSA® listed enclosure products Types 1, 3, 3R, 4, 4X, and 12.

Complies with:

1. EN / IEC 60204-1 and 60529 Type IP66
2. RoHS directive



### COLOR

ANSI 61 dark gray

### ADDITIONAL MATERIALS

Blended neoprene/EPDM gasket

### MATERIAL

Polycarbonate