



FB-6N



VIDEO

Product Description

Single gang rectangular floor box assembly with a nickel plated flip-lid cover for a decorative style device

Catalog #: FB-6N

Height: 4.31 in.

Width: 2.50 in.

Depth: 3.50 in.

Volume: 24.5 cu. in.

Type of Installation: Old or New Work

Carton Quantity: 6

Carton Weight: 10 lb.

UPC: 085339972341

UNSPSC: 39121307

Patents:

U.S. Patent No. 6,365,831 B1

Country of Origin: China

FEATURES

Designed for use in wood floor construction and can be installed with multiple floor substrate materials, meets scrub-water exclusion test, tamper resistant receptacle, simple exterior shape for easy cut-in application

APPLICATION

Floor box assembly for residential wood floor cut-in application for use with nonmetallic sheathed cable. Used in areas of the home with large floor space openings where additional electric outlets are required by National Electrical Code to minimize long extension cord runs.

STANDARDS

ANSI / UL514C: File No. QCMZ.E30594



LISTED FLOOR BOX 714L

COLOR

Black

MATERIAL

Polycarbonate box and nickel plated brass cover

MOUNTING

Metal wing brackets/nonmetal flange floor or ceiling compression

ADDITIONAL MATERIALS

Closed cell rubber gasket

Galvanized steel dust plate with plated carbon steel fasteners

Nonmetallic pop-in cable clamp

Plated carbon steel fasteners