



P-643HQT



Product Description

Three gang electrical box for use with nonmetallic sheathed cable

Brand: flexBOX®
Catalog #: P-643HQT

Carton Quantity: 20
Carton Weight: 11 lb.

Height: 3-3/4 in.
Width: 5-13/16 in.
Depth: 3-9/16 in.
Volume: 64 cu. in.
Type of Installation: New Work
Wall Box
Number of Gangs: 3

UPC: 085339463047
UNSPSC: 39121308
Patents:
U.S. Patent No. 6,365,831 B1
Country of Origin: United States of America

FEATURES

Quick Thread device holes, leveling ribs

APPLICATION

New work residential construction 2 HR fire resistive walls

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 24 inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Black

ADDITIONAL MATERIALS

Galvanized snap in bracket

MATERIAL

Polycarbonate

MOUNTING

Stud face mount steel hanger bracket with 1/2" offset and opposite side drywall tabs