

[Lift Off Screw Cover](#)

[Lift Off Screw Cover w/
Window](#)

[Lift-Off Screw Cover -
Clear Polycarbonate](#)

[Hinged Screw Cover](#)

[Hinged Screw Cover w/
Window](#)

[Hinged Screw Cover -
Clear Polycarbonate](#)

[Snap Latch Hinged Cover](#)

[Snap Latch Hinged Cover
w/ Window](#)

[Snap Latch Hinged Cover
- Clear Polycarbonate](#)

[Twist Latch Hinged Cover](#)

[Twist Latch Hinged Cover
w/ Window](#)

[Twist Latch Hinged Cover
- Clear Polycarbonate](#)

AMU664LF



Image shown represents enclosure category only! Enclosure shown is flange mounted and not sized to scale for actual part number!

Optional Accessories

Painted Steel Back Panel: P66
Aluminum Back Panel: PA66
Fiberglass Back Panel: PF66
Galvannealed Back Panel: PG66
Aluminum HFP: HFPU66
Pole Mount Kit: AMPOLEMNT6

6x6x4 NEMA 4X FBRGLS ENCL QUICK-RELEASE LATCH HINGED CVR FLANGE MOUNT

Height (In.): 6.0
Width (In.): 6.0
Depth (In.): 4.0

Standard Weight (Lbs.): 3.0
UPC: 085339958208

Material of Construction:
Cover/Base - Ultraguard® Fiberglass reinforced polyester (Color RAL 7035)
Fasteners - 300 series stainless steel
Back panel inserts - Brass
Gasket - Closed cell neoprene
Feet/Flange - Polycarbonate (Color RAL 7035)

Test Spec:
Construction meets **NEMA/EMEC** Type 1, 2, 3, 4, 4X, 12 and 13
UL® 508A listed; Type 1, 2, 3, 3R, 4, 4X, 12, and 13
CSA-C22 No. 14; Type 1, 2, 3, 3R, 4, 4X, 12, and 13
IEC60529 Type IP66



Compliant with **RoHS** (Restriction of Hazardous Substances)



[Cad Drawing](#)

[PDF Drawing](#)