



Overview

Altronix Sav182D Power Supply provides 12VDC distributed via eighteen (18) Class 2 Rated PTC protected power limited outputs for powering surveillance cameras.



Specifications

Input:

- 115VAC 60Hz, 3 amp /230VAC 50Hz, 1.5 amp.

Output:

- 12VDC @ 11 amp total output current
(0.61 amp per device, 2.5 amp max.).
- Eighteen (18) Class 2 Rated PTC protected power limited outputs.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 68.24 BTU/Hr.
- System AC input VA requirement:
 - 115VAC: 345VA.
 - 230VAC: 330VA.

Mechanical:

- NEMA1 enclosure.
- Enclosure Dimensions (H x W x D approx.):
13.5" (342.9mm) x 13" (330.2mm)
x 3.25" (82.55mm)
- Product weight (approx.): 7.8 lbs. (3.54 kg.).
- Shipping weight (approx.): 8.7 lbs. (3.95 kg.).

Features:

- Eighteen (18) power LEDs.
- Power ON/OFF switch.
- Field installable 3-wire line cord with integral strain relief.
- Unit maintains camera synchronization.
- Ease of installation saves time & eliminates costly labor.

Agency Approvals



UL Listed for Commercial CCTV Equipment
(UL 2044).



CUL Listed - CSA Standard C22.2
No.1-98, Audio, Video and Similar
Equipment.

Enclosure Dimensions (H x W x D) (approximate):

13.5" (342.9mm) x 13" (330.2mm) x 3.25" (82.55mm)

