

# AE Series 60 Amp Pin and Sleeve Receptacles Connectors and Plugs

## Weatherproof

600 Vac, 250 Vdc. Pressure Wire Terminals. Wire Size Range: #8—#4



Grounding Style	Wire/Pole	Spring Door Receptacle Only	Screw Cap Receptacle Only	Connector Body Only	Clamping Ring Plug	Plug Cable Dia. (Inches)
Style 1 (Shell Only)	2W, 2P	AE621	AE627	APR6252	AEP6252	1.000 to 1.312
	3W, 3P	AE631	AE637	APR6352	AEP6352	1.000 to 1.312
	4W, 4P	AE641	AE647	APR6452	AEP6452	1.000 to 1.312
Style 2 (Shell and Extra Pole)	2W, 3P	AE632	AE638	APR6362	AEP6362	1.000 to 1.312
	3W, 4P	AE642	AE648	APR6462	AEP6462	1.000 to 1.312

### AE Series Mounting Boxes



Hub Size (Inches)	AEE	AERH	AERC	AERA	AJA*	AJA Adapter
1	AEE36	AERH36	AERC36	AERA36	AJA310	AJA100
1-1/4	AEE46	AERH46	AERC46	AERA46	AJA410	AJA100
1-1/2	AEE56	AERH56	AERC56	AERA56	AJA510	AJA100
2	—	—	—	—	AJA610	AJA100

### 60 Amp Interiors †



Grounding Style	Wire/Pole	Interior Style 1		Interior Style 2	
		Receptacle	Plug	Receptacle	Plug
Style 1 (Shell Only)	2W, 2P	AEI-621	AEPI-621	—	—
	3W, 3P	AEI-631	AEPI-631	—	—
	4W, 4P	AEI-641	AEPI-641	—	—
Style 2 (Shell and Extra Pole)	2W, 3P	—	—	AEI-632	AEPI-632
	3W, 4P	—	—	AEI-642	AEPI-642

\* AJA Feed Thru box furnished with one close-up plug in bottom recessed hub.

† Pins and sleeves are not sold separately.