



MCI-A Cable Ranges

Style	Part Number (ST = Snap-Tite®)	Knock-Out Size	Cable Range (Aluminum)	Cable Range (Steel)	End Stop Diameter	Number of Cables	Insulated Throat	Aluminum	Steel	Healthcare Facilities
Snap2Tite® Connectors (Push-In Type)	38A	1/2	0.440 - 0.550			1	*	*		*
	38AST	1/2	0.440 - 0.550			1	*	*		*
	380AST	1/2	0.440 - 0.550			1	*	*		*
	3810AST	1/2	0.370 - 0.510		0.310	1	*	*		*
	3838AST	1/2	0.440 - 0.550			2	*	*		*
	383810AST	1/2	0.370 - 0.510		0.310	2	*	*		*
	40AST	1/2	0.440 - 0.550			1	*	*		*
	400AST	1/2	0.440 - 0.550			1	*	*		*
	4010AST	1/2	0.405 - 0.580			1	*	*		*
	4040AST	1/2	0.440 - 0.550			2	*	*		*
	404010AST	1/2	0.405 - 0.580			2	*	*		*
	5010AST	1/2	0.610 - 0.780			1	*	*		*
	505010AST	3/4	0.590 - 0.820			2	*	*		*
	7510AST	3/4	0.895 - 1.110			1	*	*		*
SADDLEGRIP® Connectors (Straight and Duplex)	SG38	1/2	0.430 - 0.580		0.400	1	*	*		*
	SG38A	1/2	0.430 - 0.580		0.400	1	*	*		*
	SG38AST	1/2	0.430 - 0.580		0.400	1	*	*		*
	SG380	1/2	0.430 - 0.580		0.400	1	*	*		*
	SG380A	1/2	0.430 - 0.580		0.400	1	*	*		*
	SG380AST	1/2	0.430 - 0.580		0.400	1	*	*		*
	SG3838	1/2	0.430 - 0.510			2	*	*		*
	SG3838A	1/2	0.430 - 0.510			2	*	*		*
	SG3838ST	1/2	0.430 - 0.510			2	*	*		*
	SG3838AST	1/2	0.430 - 0.510			2	*	*		*
	SG40	1/2	0.630 - 0.770			1	*	*		*
	SG50	1/2	0.680 - 0.850			1	*	*		*
	SG50A	1/2	0.680 - 0.850			1	*	*		*
	SG50ST	1/2	0.680 - 0.850			1	*	*		*
SG50AST	1/2	0.680 - 0.850			1	*	*		*	
Two Screw Clamp Type Connectors	840	1/2	0.440 - 0.520		0.400	1	*	*		*
	840ST	1/2	0.440 - 0.520		0.400	1	*	*		*
	8400	1/2	0.440 - 0.520		0.400	1	*	*		*
	8400ST	1/2	0.440 - 0.520		0.400	1	*	*		*
90° Two Screw Clamp Type Connectors	85	1/2	0.370 - 0.510			1	*	*		*
	85ST	1/2	0.370 - 0.510			1	*	*		*
	850	1/2	0.440 - 0.595			1	*	*		*
	850A	1/2	0.440 - 0.595			1	*	*		*
	850ST	1/2	0.440 - 0.595			1	*	*		*
	850AST	1/2	0.440 - 0.595			1	*	*		*
	851	1/2	0.680 - 0.770			1	*	*		*
	851A	1/2	0.680 - 0.770			1	*	*		*
	851ST	1/2	0.680 - 0.770			1	*	*		*
851AST	1/2	0.680 - 0.770			1	*	*		*	
Clamp Type Two Cable Connectors	846	1/2	0.370 - 0.580	0.370 - 0.580		2	*	*	*	*
	846A	1/2	0.370 - 0.580	0.370 - 0.580		2	*	*	*	*
	846ST	1/2	0.370 - 0.580	0.370 - 0.580		2	*	*	*	*
	846AST	1/2	0.370 - 0.580	0.370 - 0.580		2	*	*	*	*
	84690	1/2	0.370 - 0.580	0.370 - 0.580		2	*	*	*	*
	84690ST	1/2	0.370 - 0.580	0.370 - 0.580		2	*	*	*	*
Single Screw Clamp Type Connectors	L15AST	1/2	0.405 - 0.580	0.405 - 0.580		1	*	*	*	*
	L16	1/2	0.405 - 0.650	0.405 - 0.650	0.400	1	*	*	*	*
	L16ST	1/2	0.405 - 0.650	0.405 - 0.650	0.400	1	*	*	*	*
	L160	1/2	0.370 - 0.510	0.405 - 0.690	0.305	1	*	*	*	*
	L160ST	1/2	0.370 - 0.510	0.405 - 0.690	0.305	1	*	*	*	*