



Steel Pan Fan & Fixture Mounting Boxes

Ceiling fan/fixture pan boxes mount directly to a joist for a secure installation. Steel box.




CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION/STYLE	UNIT PKG	STD PKG	DIM A	DIM B
FBS405	76185	For 1/2" or 5/8" Drywall 6.0 Cu. In.	25	25	.570	4.250
FBS407	76187	For 5/8" Drywall 8.0 Cu. In.	25	25	.660	4.250
FBS405T*	40500	For 1/2" or 5/8" Drywall 6.0 Cu. In.	25	25	.570	4.250
FBS407T*	40700	For 5/8" Drywall 8.0 Cu. In.	25	25	.720	4.250


*Fan/fixture mounting bracket attaches to box through threaded openings using provided #10 screws.

Refer to chart on page N-28 for load ratings and number of single conductors.

PATENTS PENDING.



FBS405



FBS405T

Each fan/fixture box includes...

Installation screws, installed NM cable connector, mud cover, additional KOs, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Features and Benefits

- No loose parts to misplace – totally self-contained!
- Center screw is shipped-in-place
- Competitively priced
- Protective plastic tips on the installation screws for added safety
- Plated steel finish
- Combination hex/Phillips head screws for easy installation with power screwdrivers
- Fan/fixture installation screws are “parked”...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

FBS405 Installation Instructions



1
Install FBS405 on joist using shipped-in-place screw near center of box.



2
Remove parked-in-place screws to mount bracket

Drill (2) 1/8" diameter holes into joist through the elongated openings on each side of box. Remove the (2) long screws noted above to mount the fan/fixture bracket.



3
Mount the fan/fixture bracket into the drilled holes. And you're ready to install the fan or fixture.

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.