



Flat Plate Fittings

P1062, P1063, P1064, P1964, P2471, P2490 




Part No.	Bolt Size	Hole Size	Wt/100 pcs Lbs (kg)
P1062	5/16"	1 1/32"	18 (8.2)
P1063	3/8"	7/16"	18 (8.2)
P1064	1/2"	9/16"	17 (7.7)
P1964	5/8"	1 1/16"	16 (7.3)
P2471	3/4"	1 3/16"	15 (6.8)
P2490	7/8"	1 5/16"	14 (6.4)

P1959, P1960, P1961 




Part Number	U.S. Std. Thd Size	Wt/100 pcs Lbs (kg)
P1959	3/8" - 16	21 (9.5)
P1960	1/2" - 13	20 (9.1)
P1961	5/8" - 11	19 (8.6)

P2862, 2863, 2864 



Part Number	Bolt Size	Hole Size	Wt/100 pcs Lbs (kg)
P2862	5/16"	1 1/32"	18 (8.2)
P2863	3/8"	7/16"	18 (8.2)
P2864	1/2"	9/16"	17 (7.7)


P1065 



Material: 3/8" (9.5 mm) thick


Wt/100 pcs: 38 Lbs (17.2 kg)

P1924 




Wt/100 pcs: 35 Lbs (15.9 kg)

P2325 




Wt/100 pcs: 55 Lbs (24.9 kg)

P2324 




Wt/100 pcs: 75 Lbs (34.0 kg)

P1066 




Wt/100 pcs: 56 Lbs (25.4 kg)

P1925 




Wt/100 pcs: 50 Lbs (22.7 kg)

P1067 




Wt/100 pcs: 78 Lbs (35.4 kg)

P2079 




Wt/100 pcs: 73 Lbs (33.1 kg)

P1941 




Wt/100 pcs: 94 Lbs (42.6 kg)

P1036 




Wt/100 pcs: 58 Lbs (26.3 kg)

P1380 A 




Wt/100 pcs: 80 Lbs (36.3 kg)

P1334 



Wt/100 pcs: 70 Lbs (31.8 kg)

P1380 



Wt/100 pcs: 105 Lbs (47.6 kg)

Standard Dimensions for 1 5/8" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)

Hole Diameter: 5/16" (14.3mm); Hole Spacing - From End: 1 3/16" (20.6mm); Hole Spacing - On Center: 1 7/8" (47.6mm); Width: 1 5/8" (41.3mm); Thickness: 1/4" (6.4mm)