


"U" Shape Fittings


P2800

EG, GR, HG




Part Number	Bolt Size (in)	Hole Size (in)	Wt/100 pcs Lbs (kg)
P2800-25	1/4"	9/32"	14 6.4
P2800-37	3/8"	7/16"	14 6.4
P2800-50	1/2"	9/16"	13 5.9
P2800-62	5/8"	11/16"	13 5.9
P2800-75	3/4"	13/16"	13 5.9

P1363A THRU P1363E



Part Number	"A" In (mm)	Wt/100 pcs Lbs (kg)
P1363A	4 101.6	78 35.4
P1363B	5 127.0	89 40.4
P1363C	6 152.4	101 45.8
P1363D	7 177.8	112 50.8
P1363E	8 203.2	124 56.2


P1320



Wt/100 pcs: 63 Lbs (28.6 kg)

P1376


EG, GR, HG



Wt/100 pcs: 128 Lbs (58.1 kg)

P4376


EG, GR, HG



Wt/100 pcs: 85 Lbs (38.6 kg)

P1376A


EG, GR, HG



Wt/100 pcs: 197 Lbs (89.4 kg)

P4376A


EG, GR, HG



Wt/100 pcs: 130 Lbs (59.0 kg)

P1377, P4377, P5077, P5577


EG, GR, HG



Part Number	For Use With	"A" in (mm)	Wt/100 pcs Lbs (kg)
P1377	P1000, P1100, P2000	1 9/16 39.7	265 120
P4377	P3300, P4000, P4100	1 5/16 23.8	176 80
P5077	P5000	3 3/16 81.0	390 177
P5577	P5500	2 3/8 60.3	310 141

P1047


EG, GR, HG



Wt/100 pcs: 88 Lbs (39.9 kg)


P3047

EG, GR, HG



Wt/100 pcs: 84 Lbs (38.1 kg)


P976



Wt/100 pcs: 71 Lbs (32.2 kg)

P4047


EG, GR, HG



Wt/100 pcs: 71 Lbs (32.2 kg)

P1455


EG, GR, HG



Wt/100 pcs: 58 Lbs (26.3 kg)

P5547

EG, GR, HG



Wt/100 pcs: 108 Lbs (49.0 kg)

Standard Dimensions for 1 5/8" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)

Hole Diameter: 5/16" (14.3mm); Hole Spacing - From End: 1 3/16" (20.6mm); Hole Spacing - On Center: 1 7/8" (47.6mm); Width: 1 5/8" (41.3mm); Thickness: 1/4" (6.4mm)