

AFC Non-Metallic Whips Type UL

Specification Description

Specification	Non-Metallic Whips
Conduit	Type LFNC-B, Non-metallic Liquidtight
Conductors	THHN/THWN 8 & 10 AWG
Maximum Temperature Rating	90°C (dry) 75°C (wet)
Grounding	NEC® 250.118(1)
Maximum Voltage Rating	600V

References & Ratings

- UL File Reference E96572
- NEC® 410, 430, 440, 250, 356
- RoHS Compliant



Non-metallic Liquidtight Whips (Standard Configurations)

Product Code	Trade Size (inches)	Length (feet)	No. of Cond.	AWG (cond. size)	Put Up
8014	1/2"	4'	3	10	10 per box
8015	1/2"	6'	3	10	10 per box
8016	3/4"	4'	3	8	10 per box
8017	3/4"	6'	3	8	8 per box
8021	1/2"	4'	3	10	20 bulk
8022	1/2"	6'	3	10	15 bulk
8023	3/4"	4'	3	8	10 bulk
8024	3/4"	6'	3	8	10 bulk

Whips come with Black, Red, Green THHN/THWN conductors.

Other conductor colors available by special request.

All whips come with one straight non-metallic liquidtight connector and one 90° angle non-metallic liquidtight connector.