

SENSORS
PLASTIC FIBERS
GLASS FIBERS



Indicates lenses available for model. See page 207 for details.

M600 Available 315° C models. Add **M600** to end of model number (example, BA23SM600).

M900 Available 480° C models. Add **M900** to end of model number (example, BA23SM900).

Model Number	Drawing & Dimensions	Core Dia. (mm)	Min. Bend Radius (mm)	Features	Typical Range (mm)
Standard	BA23S 	3.18	19	• 90° Angle 	
	BAT23S 	3.18	19	• 90° Angle/Thread 	
	BF23P 	3.18	19	• Smooth ferrule 	
	BMT.442P 	0.69	9.5	• Miniature thread	
	BT23S 	3.18	19	• Thread 	
	BTA23S 	3.18	19	• Thread/90° Angle 	
Miniature Probe	BAM.752S 	1.17	19	• ø 1.5 mm non-bendable probe; 90° angle 	
	BM.752S 	1.17	19	• ø 1.5 mm non-bendable probe 	
	BMP.753P 	1.17	9.5	• ø 1.5 mm non-bendable probe	
Area Sensing (Array)	BR2.53S 	3.96	19	• Straight exit; 38 mm width 	
	BR23S 	3.18	19	• Straight exit; 10 mm width 	