

## EZ-SCREEN Accessory Cordsets

For 8-Pin Receivers

8-Pin Threaded M12/Euro-Style Splitter Cordsets—Flat Junction					
Model	Trunk (Male)	Branches (Female)	Dimensions	Pinout	
<b>CSB-M1280M1280</b>	No trunk	No branches		<p><b>Female</b></p>	
<b>CSB-M1281M1281</b>	0.3 m (1 ft)	2 x 0.3 m (1 ft)			<p><b>Male</b></p>
<b>CSB-M1288M1281</b>	2.44 m (8 ft)				
<b>CSB-M12815M1281</b>	4.57 m (15 ft)				
<b>CSB-M12825M1281</b>	7.62 m (25 ft)				
<b>CSB-UNT825M1281</b> <sup>3</sup>	7.62 m (25 ft) Unterminated			<p>1 = Brown      5 = Black                  2 = Or/Bk      6 = Blue                  3 = Orange     7 = Gn/Ye                  4 = White      8 = Violet</p>	

8-Pin Threaded M12/Euro-Style Cordsets—Double Ended					
Model (8-pin/8-pin) <sup>4</sup>	Length	Style	Dimensions	Pinout	
<b>DEE2R-81D</b>	0.31 m (1 ft)	Female Straight/ Male Straight		<p><b>Female</b></p>	
<b>DEE2R-83D</b>	0.91 m (3 ft)				
<b>DEE2R-88D</b>	2.44 m (8 ft)				
<b>DEE2R-815D</b>	4.57 m (15 ft)				
<b>DEE2R-825D</b>	7.62 m (25 ft)				
<b>DEE2R-850D</b>	15.2 m (50 ft)				
<b>DEE2R-875D</b>	22.9 m (75 ft)				
<b>DEE2R-8100D</b>	30.5 m (100 ft)			<p><b>Male</b></p> <p>1 = White      5 = Gray                  2 = Brown     6 = Pink                  3 = Green      7 = Blue                  4 = Yellow     8 = Red</p>	

<sup>3</sup> Standard cordsets are yellow PVC with black overmold. For black PVC and overmold, add suffix B to model number (example, CSB-M1280M1280B).

<sup>4</sup> Standard cordsets are yellow PVC with black overmold. For black PVC and overmold, add suffix "B" to model number (example, DEE2R-81DB)