

## 8-Pin Threaded M12/Euro-Style Cordsets with Shield

**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut  
**Conductors:** 24 AWG (shielded), gold-plated contacts  
**Voltage/Current Rating:** 75V ac/dc, 2.0 A  
**Temperature:** -40° to +105° C      **Environmental Rating:** IP67

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
Straight	1.83 m	MQDC-806	5.60 mm		<b>Female</b>  1 = White    5 = Gray 2 = Brown    6 = Pink 3 = Green    7 = Blue 4 = Yellow    8 = Shield	<ul style="list-style-type: none"> <li>• LT3</li> <li>• LG5</li> <li>• LG10</li> </ul>
	4.58 m	MQDC-815				
	9.14 m	MQDC-830				

## 8-Pin Threaded M12/Euro-Style Cordsets with Shield

**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut  
**Conductors:** 24 AWG (shielded), gold-plated contacts  
**Voltage/Current Rating:** 75V ac/dc, 2.0 A  
**Temperature:** -40° to +105° C      **Environmental Rating:** IP67

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
Straight	1.83 m	MAQDC-806	5.60 mm		<b>Female</b>  1 = White    5 = Gray 2 = Brown    6 = Pink 3 = Green    7 = Blue 4 = Yellow    8 = Red	<ul style="list-style-type: none"> <li>• EZ-ARRAY Emitters/Receivers</li> </ul>
	4.58 m	MAQDC-815				
	9.14 m	MAQDC-830				
	15.2 m	MAQDC-850				

## 8-Pin Threaded M12/Euro-Style Cordsets with Shield

**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut  
**Conductors:** 24 AWG (shielded), gold-plated contacts  
**Voltage/Current Rating:** 60V ac/75V dc, 2.0 A  
**Temperature:** -40° to +80° C      **Environmental Rating:** IP67

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
Straight	1.83 m	MQLH-806-F	6.00 mm		<b>Female</b>  1 = White    5 = Gray 2 = Brown    6 = Green 3 = Shield    7 = Blue 4 = Yellow    8 = Shield	<ul style="list-style-type: none"> <li>• LH</li> </ul>
	4.58 m	MQLH-815-F				
	9.14 m	MQLH-830-F				