

MBCC-506



Mini-style Quick Disconnect Cable
 5 Pin Female Pin-out Straight Connector
 2 m (6.5 ft) in Length
 Nylon coupling nut
 Part Number: 32297

CERTIFICATIONS



SPECIFICATIONS

IEC IP68	N
IEC IP69K	N
Secondary Connector (SC) Type (or Branch 1 connector)	Flying Leads
IEC IP67	Y
	80
DC Voltage/current	300V/9A
Minimum Temp. (Celsius)	-40
UL Label Part Number	191157.JPG
Voltage Rating	300
Current Rating	9
AC Voltage/current	300V/9A
Cable PN (Trunk cable for splitter cordsets)	138811
Coupling Material/Color	Nylon Black
Connector Body Material/Color	PUR Black
Orientation	Straight
Gender	Female
Coupling Method	7/8"-16
Number of Contacts	5
Number of connectors	1
Number of Conductors	5
Shield/No Shield	No Shield
Cordset Length (m)	1.83
Outside Cable Diameter (mm)	7
Cable Jacket Color	Black
AWG	18
Cable Jacket Material	PVC
Primary Connector Type	MINI