

| 12-Pin QD to DB15 Cordsets |        |          |                |                 |  |        |               |
|----------------------------|--------|----------|----------------|-----------------|--|--------|---------------|
| Style                      | Length | Model    | Cable Diameter | Dimensions (mm) |  | Pinout | Used With     |
| Straight/<br>DB15          | 2.00 m | P4C06SIM | 6.9 mm         |                 |  | Female | • P4 to PPSIM |
|                            | 7.00 m | P4C23SIM |                |                 |  |        |               |
|                            | 10.0 m | P4C32SIM |                |                 |  | Male   |               |

| 3-Pin Micro-Style Cordsets  |        |            |                |                 |  |                                |  |
|---|--------|------------|----------------|-----------------|--|--------------------------------|--|
| <p><b>Cable:</b> PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut<br/> <b>Conductors:</b> 22 AWG, gold-plated contacts<br/> <b>Voltage/Current Rating:</b> 250V ac/dc, 4.0 A<br/> <b>Temperature:</b> -40 to +80° C      <b>Environmental Rating:</b> IP67</p> |        |            |                |                 |  |                                |  |
| Style   | Length | Model      | Cable Diameter | Dimensions (mm) | Pinout   | Used With                      |  |
| Straight  | 1.83 m | MQDC-306   | 5.20 mm        |                 |  | • MINI-BEAM ac SM2A312 sensors |  |
|   | 4.57 m | MQDC-315   |                |                 |  |                                |  |
|   | 9.14 m | MQDC-330   |                |                 |  |                                |  |
| Right-Angle   | 1.83 m | MQDC-306RA | 5.20 mm        |                 | <p>1 = Green<br/>2 = Red/Black<br/>3 = Red/White</p> |                                |  |
|   | 4.57 m | MQDC-315RA |                |                 |  |                                |  |
|   | 9.14 m | MQDC-330RA |                |                 |  |                                |  |

| 4-Pin Micro-Style Cordsets  |        |            |                |                 |  |   |  |
|---|--------|------------|----------------|-----------------|--|---|--|
| <p><b>Cable:</b> PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut<br/> <b>Conductors:</b> 22 AWG, gold-plated contacts<br/> <b>Voltage/Current Rating:</b> 250V ac/dc, 4.0 A<br/> <b>Temperature:</b> -40° to +105° C      <b>Environmental Rating:</b> IP67</p> |        |            |                |                 |  |   |  |
| Style   | Length | Model      | Cable Diameter | Dimensions (mm) | Pinout   | Used With   |  |
| Straight  | 1.83 m | MQAC-406   | 5.70 mm        |                 |  | <ul style="list-style-type: none"> <li>• QS18 ac/dc sensors</li> <li>• Q45 ac series (suffix Q1)</li> <li>• S18, M18, T18, Q25, S30, T30 &amp; Q40 ac sensors (suffix Q1)</li> <li>• Q60</li> </ul> |  |
|   | 4.57 m | MQAC-415   |                |                 |  |   |  |
|   | 9.14 m | MQAC-430   |                |                 |  |   |  |
| Right-Angle   | 1.83 m | MQAC-406RA | 5.70 mm        |                 | <p>1 = Red/Black<br/>2 = Red/White<br/>3 = Red<br/>4 = Green</p> |   |  |
|   | 5.00 m | MQAC-415RA |                |                 |  |   |  |
|   | 9.14 m | MQAC-430RA |                |                 |  |   |  |