

4-Pin Euro-Style Splitter Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut
Conductors: 22 AWG high-flex stranded, gold-plated contacts
Voltage Rating: 250V ac/300V dc
Temperature: -40° to +90° C

Connections				
Pinout	Model	Branches	Trunk	Used With
<p>Male</p> <p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black</p>	CSB-M1240M1240*	4-Pin Euro QD No Branch Female	No Trunk Male	<ul style="list-style-type: none"> Sensors w/4-Pin Euro QD EZ-LIGHT
	CSB-M1241M1241	4-Pin Euro QD 2 x 0.3 m Female	0.3 m Male	
	CSB-M1248M1241		2.5 m Male	
	CSB-M12415M1241		5.0 m Male	
	CSB-M12425M1241		8.0 m Male	
	CSB-UNT425M1241		8.0 m Unterminated	
Dimensions				

* CSB-M1240M1240 replaces model number MDCVB4T.

5-Pin Euro-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut
Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts
Voltage Rating: 250V ac/300V dc
Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
<p>Female</p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>	Straight	MQDC1-501.5	0.5 m		<ul style="list-style-type: none"> MINI-BEAM <i>Expert</i> QS30 PicoDot Q45 Laser Retro R55F SL30 & SL30E SL10 & SL10E VTB (2-color) SLC1 Q60 PVD STB K50 K80 DX80 DX81 DX85 EZ-LIGHT
		MQDC1-515	5 m		
		MQDC1-530	9 m		
	Right-Angle	MQDC1-506RA	2 m		
		MQDC1-515RA	5 m		
		MQDC1-530RA	9 m		