

MQDC1-515



Euro-style Quick Disconnect Cable
 5 Pin Straight Connector
 5 m (15 ft) in Length
 Chrome plated brass coupling nut
 Part Number: 47812

SPECIFICATIONS

IEC IP68	N
IEC IP69K	N
Secondary Connector (SC) Type (or Branch 1 connector)	Flying Leads
IEC IP67	Y
	105
DC Voltage/current	250V/4A
Minimum Temp. (Celsius)	-40
AC Voltage/current	250V/4A
Cable PN (Trunk cable for splitter cordsets)	135005
Coupling Material/Color	Nickel Plated Brass
Connector Body Material/Color	PUR Black
Orientation	Straight
Gender	Female
Coupling Method	M12 Single Key
Number of Contacts	5
Number of connectors	1
Number of Conductors	5
Shield/No Shield	No Shield
Cordset Length (m)	4.57
Outside Cable Diameter (mm)	5.6
Cable Jacket Color	Black
AWG	22
Cable Jacket Material	PVC
Primary Connector Type	EURO