

12-Pin QD to DB15 Cordsets							
Style	Length	Model	Cable Diameter	Dimensions (mm)		Pinout	Used With
Straight/ DB15	2.00 m	P4C06SIM	6.9 mm			Female Male 	<ul style="list-style-type: none"> • P4 to PPSIM
	7.00 m	P4C23SIM					
	10.0 m	P4C32SIM					

3-Pin Micro-Style Cordsets							
Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut Conductors: 22 AWG, gold-plated contacts Voltage/Current Rating: 250V ac/dc, 4.0 A Temperature: -40 to +80° C Environmental Rating: IP67							
Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With	
Straight	1.83 m	MQDC-306	5.20 mm		Female 	<ul style="list-style-type: none"> • MINI-BEAM ac SM2A312 sensors 	
	4.57 m	MQDC-315					
	9.14 m	MQDC-330					
Right-Angle	1.83 m	MQDC-306RA	5.20 mm		1 = Green 2 = Red/Black 3 = Red/White		
	4.57 m	MQDC-315RA					
	9.14 m	MQDC-330RA					

4-Pin Micro-Style Cordsets							
Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut Conductors: 22 AWG, gold-plated contacts Voltage/Current Rating: 250V ac/dc, 4.0 A Temperature: -40° to +105° C Environmental Rating: IP67							
Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With	
Straight	1.83 m	MQAC-406	5.70 mm		Female 	<ul style="list-style-type: none"> • QS18 ac/dc sensors • Q45 ac series (suffix Q1) • S18, M18, T18, Q25, S30, T30 & Q40 ac sensors (suffix Q1) • Q60 	
	4.57 m	MQAC-415					
	9.14 m	MQAC-430					
Right-Angle	1.83 m	MQAC-406RA	5.70 mm		1 = Red/Black 2 = Red/White 3 = Red 4 = Green		
	5.00 m	MQAC-415RA					
	9.14 m	MQAC-430RA					