




MQDC-515



Micro-style Quick Disconnect Cable
5-Pin Straight Connector
5 m (15 ft) in Length
Part Number: 30623

CERTIFICATIONS



SPECIFICATIONS

IEC IP68	N
IEC IP69K	N
Secondary Connector (SC) Type (or Branch 1 connector)	Flying Leads
IEC IP67	Y
	105
DC Voltage/current	250V/4A
Minimum Temp. (Celsius)	-40
UL Label Part Number	191157.JPG
Voltage Rating	250
Current Rating	4
AC Voltage/current	250V/4A
Cable PN (Trunk cable for splitter cordsets)	138814
Coupling Material/Color	Nickel Plated Brass
Connector Body Material/Color	PUR Black
Orientation	Straight
Gender	Female
Coupling Method	1/2"-20 Dual Key
Number of Contacts	5
Number of connectors	1
Number of Conductors	5
Shield/No Shield	No Shield
Cordset Length (m)	5
Outside Cable Diameter (mm)	5.6
Cable Jacket Color	Black
AWG	22
Cable Jacket Material	PVC
Primary Connector Type	MICRO

