

MQDC-WDSS-0530



Euro-style Quick Disconnect Cable
 5-Pin Straight Connector for F&B Applications
 9 m (30 ft) in Length abrasion resistant PVC cable
 Stainless Steel hex coupling nut and EPDM o-ring
 Part Number: 88517

SPECIFICATIONS

IEC IP68	N
IEC IP69K	Y
Secondary Connector (SC) Type (or Branch 1 connector)	Flying Leads
IEC IP67	Y
	105
DC Voltage/current	300 Vdc/4A
Minimum Temp. (Celsius)	-40
Cable PN (Trunk cable for splitter cordsets)	177014
Coupling Material/Color	300 Series Stainless
Connector Body Material/Color	PVC Black
Orientation	Straight
Gender	Female
Coupling Method	M12 Single Key
Number of Contacts	5
Number of connectors	1
Number of Conductors	5
Shield/No Shield	No Shield
Cordset Length (m)	9
Outside Cable Diameter (mm)	5.2
Cable Jacket Color	Black
AWG	22
Cable Jacket Material	PVC
Primary Connector Type	EURO