

## BNC to 4-Pin Threaded M8/Pico-Style Cordsets with Shield

**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut on QD end

**Conductors:** 26 AWG

**Voltage/Current Rating:** 125V ac/125V dc, 4.0 A

**Temperature:** -40° to +105° C

**Environmental Rating:** IP67

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
BNC/ Pico QD Straight	2.00 m	PKG4M-2/CS	4.40 mm		<p><b>Female</b></p> <p>1 = Brown    3 = Blue 2 = Not Used    4 = Drain</p> <p><b>Male</b></p>	• IP68 Sealed P4
	5.00 m	PKG4M-5/CS				
	9.00 m	PKG4M-9/CS				

## Communication Cordsets

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
5-Pin M12/ Euro-Style, Straight	1.83 m	MQDMC-506	5.60 mm		<p><b>Male</b></p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>	• EZ-ARRAY to INTUSB485-1 USB Serial Adapter
	4.57 m	MQDMC-515				
	9.14 m	MQDMC-530				
5-Pin M12/ Euro-Style, Right-Angle	1.83 m	MQDMC-506RA	5.60 mm		<p><b>Male</b></p> <p>1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray</p>	• EZ-ARRAY to INTUSB485-1 USB Serial Adapter
	4.57 m	MQDMC-515RA				
	9.14 m	MQDMC-530RA				