



MQVR3S-515



Micro-style Quick Disconnect Cable With Shield
5 Pin Straight Connector
5 m (15 ft) in Length
Nickel-Plated Brass Coupling Nut
Part Number: 72673

SPECIFICATIONS

IEC IP68	N
IEC IP69K	N
Secondary Connector (SC) Type (or Branch 1 connector)	Flying Leads
IEC IP67	Y
	105
Minimum Temp. (Celsius)	-40
Cable PN (Trunk cable for splitter cordsets)	60809
Coupling Material/Color	Nickel Plated Brass
Connector Body Material/Color	PUR Black
Orientation	Straight
Gender	Female
Coupling Method	1/2"-20 Dual Key
Number of Contacts	5
Number of connectors	1
Number of Conductors	5
Shield/No Shield	Shield
Cordset Length (m)	4.57
Outside Cable Diameter (mm)	6.1
Cable Jacket Color	Gray
AWG	22
Cable Jacket Material	PVC
Primary Connector Type	MICRO

