

| SMB18A | | SMB18FA | | SMB18FM | | SMB18Q | |
|---|---|--|--|---|------------------------------|---|---|
| | | | | | | | |
| All measurements in mm | | All measurements in mm | | All measurements in mm | | All measurements in mm | |
| Hole center spacing: A to B = 24.2 Hole size: A = \varnothing 4.6, B = 17.0 x 4.6, C = \varnothing 18.5 | | A = 3/8 - 16 x 50.8 Hole size: B = \varnothing 18.1 | | N/A | | Hole center spacing: A to B = 24.2 Hole size: A = \varnothing 4.6, B = 17.0 x 4.6, C = \varnothing 19.0 | |
| <ul style="list-style-type: none"> • Right-angle mounting bracket with a curved slot for versatile orientation • 12-ga. stainless steel, 18 mm sensor mounting hole • Clearance for M4 (#8) hardware | | <ul style="list-style-type: none"> • Swivel bracket with tilt and pan movement for precision adjustment • 18 mm sensor mounting hole • 12-ga. 304 stainless steel | | <ul style="list-style-type: none"> • Two-piece thermoplastic through-mount bracket • Mounting nut (M22 x 1.5) and outer flange (M22 x 1.5 external, M18 x 1 internal) | | <ul style="list-style-type: none"> • Right-angle flanged bracket • 18 mm sensor mounting hole • 12-ga. stainless steel | |
| Barrel Mount | | Barrel Mount | | Barrel Mount | | Barrel Mount | |
| <p>Used with</p> | | <p>Used with</p> | | <p>Used with</p> | | <p>Used with</p> | |
| QS18 MINI-BEAM M18 S18 T18 T-GAGE M18T S18U | QS18U Q45UR M18C2 Q45UR S18C2 T18U EZ-LIGHT T18 EZ-LIGHT M18 | QS18 MINI-BEAM S18/M18/T18 S18U QS18U Q45UR M18C2 | Q45UR S18C2 T18U T-GAGE M18T EZ-LIGHT M18 EZ-LIGHT T18 | QS18 M18 S18 T18 | T-GAGE M18T S18U QS18U | QS18 MINI-BEAM S18 M18 T18 S18U | QS18U Q45UR S18C2 Q45UR M18C2 T18U EZ-LIGHT T18 EZ-LIGHT M18 |
| Base Mount | | Bracket-to-Bracket | | | | Base Mount | |
| <p>Used with</p> | | <p>Used with</p> | | | | <p>Used with</p> | |
| Q25 | | SMBQS18A | SMBQS18Y | | | Q25 | |
| | | Base Mount | | | | | |
| | | <p>Used with</p> | | | | | |
| | | Q25 | | | | | |

BRACKETS
CABLES
RETROREFLECTORS
ENCLOSURES/
LENS SHIELDS
MISCELLANEOUS