

SMB30SK		SMB30SUS	SMB30UR	SMB312B
All measurements in mm		All measurements in mm	All measurements in mm	All measurements in mm
<b>Hole center spacing:</b> A = 50.8 <b>Hole size:</b> A = $\varnothing$ 7.0, B = $\varnothing$ 18.0		<b>Hole center spacing:</b> A to B = 50.8 <b>Hole size:</b> A = $\varnothing$ 7.0	<b>Hole center spacing:</b> A to B = 31.8, B to C = 19.0, A to C = 50.8, D = 50.8 <b>Hole size:</b> A, B, C = 6.9 x 32.0, D = 73 x 6.9	<b>Hole center spacing:</b> A to B = 17.3, B to C = 17.7, A to C = 35.0 <b>Hole size:</b> A = $\varnothing$ 6.9, B = 4.3 x 10.5, C = 3.1 x 15.2
<ul style="list-style-type: none"> <li>Flat-mount swivel bracket with extended range of motion</li> <li>Black reinforced thermoplastic polyester and 316 stainless steel</li> <li>Stainless steel swivel locking hardware included</li> </ul>		<ul style="list-style-type: none"> <li>Side-mount swivel bracket with extended range of motion</li> <li>Black reinforced thermoplastic polyester</li> <li>Stainless steel swivel locking hardware included</li> </ul>	<ul style="list-style-type: none"> <li>2-piece universal swivel bracket for limit-switch style sensors</li> <li>300 series stainless steel</li> <li>Stainless steel swivel locking hardware included</li> </ul>	<ul style="list-style-type: none"> <li>Right-angle</li> <li>Stainless steel base mounting bracket</li> <li>Includes mounting foot</li> </ul>
Barrel Mount		Side Mount	Side Mount	Base Mount
Used with		Used with	Used with	Used with
QS18 MINI-BEAM S18/M18/T18 T18U S18U QS18U	Q45UR S18C2 Q45UR M18C2 EZ-LIGHT T18 EZ-LIGHT M18 T-GAGE M18T	QS18 MINI-BEAM QM42/QMT42 QS18U	Q45 OMNI-BEAM Q45U Q45UR	MINI-BEAM
Base Mount				
Used with				
Q25				
Side Mount				
Used with				
QM42/QMT42				

BRACKETS

CABLES

RETROREFLECTORS

ENCLOSURES/  
LENS SHIELDS

MISCELLANEOUS