

SMBQ60	SMBQC50	SMBQS12PD	SMBQS18A
<p>All measurements in mm</p>	<p>All measurements in mm</p>	<p>All measurements in mm</p>	<p>All measurements in mm</p>
<p>Hole center spacing: A to B = 24,1 Hole size: A = \varnothing 4,5, B = 8,4 x 4,5</p>	<p>Hole center spacing: A to B = 18, B to B = 36 Hole size: A = \varnothing 4, B = 4 x 13,3</p>	<p>Hole center spacing: A to B = 14 Hole size: A = \varnothing 3,5, B = 3,5 x 10,6, C = \varnothing 13</p>	<p>Hole size: A = \varnothing 15,3</p>
<ul style="list-style-type: none"> • Right-angle bracket • 14-ga. 304 stainless steel 	<ul style="list-style-type: none"> • Multi-directional stainless steel right-angle bracket • Variety of mounting options 	<ul style="list-style-type: none"> • Right-angle, nose-mount bracket • 16-ga. 300 series stainless steel 	<ul style="list-style-type: none"> • Wrap-around protection bracket • Die-cast bracket • Base fits 18 mm threaded hole • Metal hex nut, lock washer and grommet included • Mounting holes specially designed for QS18AF sensors
Side Mount	Side Mount	Barrel Mount	Side Mount
<p>Used with</p>	<p>Used with</p>	<p>Used with</p>	<p>Used with</p>
Q60	QC50 QCX50	M12 S12	QS18 (DC only) QS18U QS18AF

