

## Right Angle Compression Connectors

INDUSTRY USE: COMMERCIAL • PROFESSIONAL AV • SECURITY

- Designed to allow for adequate cable bend radius when space is limited
- A great solution for flush mounts, TV rack mounts, plasma/LCD televisions, and dome security camera installations
- Features a positive stop design to help guide the cable into the connector and prevent it from being over-compressed
- F, RCA and BNC are available for RG59, RG6 and RGB/ mini coax cable sizes



Part#	Connector Description	Tip Req'd	Tool Req'd
FSRCA15RA	RCA 15RGB, Right Angle, Multi-piece, 22-24 AWG (Purple) - Nickel	LMTIP-RA	CPLCCT-SLM
FSBNC15RA	BNC 15RGB, Right Angle, Multi-piece, 22-24 AWG (Purple) - Nickel	LMTIP-RA	CPLCCT-SLM
FSRCA1RA	RCA 1RGB, Right Angle, Multi-piece, 25-26 AWG (Orange) - Nickel	LMTIP-RA	CPLCCT-SLM
FSBNC1RA	BNC 1RGB, Right Angle, Multi-piece, 25-26 AWG (Orange) - Nickel	LMTIP-RA	CPLCCT-SLM
FS59URA	RG59 F-type Universal Right Angle (Red) - Nickel	LMTIP-RA	CPLCCT-SLM
FSRCA59URA	RG59 RCA Universal Right Angle (Red) - Nickel	LMTIP-RA	CPLCCT-SLM
FSBNC59URA	RG59 BNC Universal Right Angle (Red) - Nickel	LMTIP-RA	CPLCCT-SLM
FS6URA	RG6 F-type Universal Right Angle (Green) - Nickel	LMTIP-RA	CPLCCT-SLM
FSRCA6URA	RG6 RCA Universal Right Angle (Green) - Nickel	LMTIP-RA	CPLCCT-SLM
FSBNC6URA	RG6 BNC Universal Right Angle (Green) - Nickel	LMTIP-RA	CPLCCT-SLM

**NOTE:** All cable for Belden compression connectors should be sized using the Belden Cable Sizing Chart located on pages 40-43 or at [www.icmcorp.net/ICM\\_techinfo.com](http://www.icmcorp.net/ICM_techinfo.com)