

BIZLINE RXP PART#	CANTEX PART#	CARLON PART #	IPEX Part#	I2of5	SIZE	BIZLINE DESCRIPTION	STD. PKG.
SCHEDULE 80 SPECIAL RADIUS ELBOWS — PLAIN END — SIZE 1½							
1509018ELB80	5121848	UB9CH	N/A	30088700023377	1½"	1-1/2-90DEG-18RAD-SCH80-ELL	EA
1509024ELB80	5121015	UB9DH	N/A	30088700013071	1½"	1-1/2-90DEG-24RAD-SCH80-ELL	EA
1509036ELB80	5121100	UB9FH	N/A	30088700013408	1½"	1-1/2-90DEG-36RAD-SCH80-ELL	EA
1509048ELB80	5121076	UB9HH	N/A	30088700013255	1½"	1-1/2-90DEG-48RAD-SCH80-ELL	EA
1509060ELB80	5121102	N/A	N/A	30088700013422	1½"	1-1/2-90DEG-60RAD-SCH80-ELL	EA
1504518ELB80	5121037	UB7CH	N/A	30088700023308	1½"	1-1/2-45DEG-18RAD-SCH80-ELL	EA
1504524ELB80	5163533	UB7DH	N/A	30088700029102	1½"	1-1/2-45DEG-24RAD-SCH80-ELL	EA
1504536ELB80	5136533	UB7FH	N/A	30088700033550	1½"	1-1/2-45DEG-36RAD-SCH80-ELL	EA
1504560ELB80	5136840	N/A	N/A	30088700947703	1½"	1-1/2-45DEG-60RAD-SCH80-ELL	EA
1503018ELB80	5136535	N/A	N/A	30088700028860	1½"	1-1/2-30-DEG-18RAD-SCH80-ELL	EA
1503024ELB80	5136536	N/A	N/A	30088700942951	1½"	1-1/2-30DEG-24RAD-SCH80-ELL	EA
150221218ELB80	5136650	N/A	N/A	30088700028969	1½"	1-1/2-22-1/2-DEG-18RAD-SCH80-ELL	EA
150221224ELB80	5136651	N/A	N/A	30088700028976	1½"	1-1/2-22-1/2-DEG-24RAD-SCH80-ELL	EA
150221236ELB80	5136652	N/A	N/A	30088700018373	1½"	1-1/2-22-1/2-DEG-36RAD-SCH80-ELL	EA
SCHEDULE 80 SPECIAL RADIUS ELBOWS — PLAIN END — SIZE 2							
2009018ELB80	5121099	UB9CJ	N/A	30088700013392	2"	2IN-90DEG-18RAD-SCH80-ELL	EA
2009024ELB80	5121019	UB9DJ	N/A	30088700013118	2"	2IN-90DEG-24RAD-SCH80-ELL	EA
2009036ELB80	5121021	UB9FJ	N/A	30088700013132	2"	2IN-90DEG-36RAD-SCH80-ELL	EA
2009048ELB80	5121075	UB9HJ	N/A	30088700013248	2"	2IN-90DEG-48RAD-SCH80-ELL	EA
2009060ELB80	5121086	N/A	N/A	30088700023346	2"	2IN-90DEG-60RAD-SCH80-ELL	EA
2004518ELB80	5136551	UB7CJ	N/A	30088700023261	2"	2IN-45DEG-18RAD-SCH80-ELL	EA
2004524ELB80	5121101	UB7DJ	N/A	30088700013415	2"	2IN-45DEG-24RAD-SCH80-ELL	EA
2004536ELB80	5121098	UB7FJ	N/A	30088700013385	2"	2IN-45DEG-36RAD-SCH80-ELL	EA
2004548ELB80	5121093	UB7HJ	N/A	30088700016591	2"	2IN-45DEG-48RAD-SCH80-ELL	EA
2004560ELB80	5136850	N/A	N/A	30088700018397	2"	2IN-45DEG-60RAD-SCH80-ELL	EA
2003018ELB80	5136553	N/A	N/A	30088700033574	2"	2IN-30DEG-18RAD-SCH80-ELL	EA
2003024ELB80	5136554	N/A	N/A	30088700028877	2"	2IN-30DEG-24RAD-SCH80-ELL	EA
2003036ELB80	5121094	UB6FJ	N/A	30088700013378	2"	2IN-30DEG-36RAD-SCH80-ELL	EA
2003060ELB80	5136750	N/A	N/A	30088700947765	2"	2IN-30DEG-60RAD-SCH80-ELL	EA
200221218ELB80	5136660	N/A	N/A	30088700018380	2"	2IN-22-1/2-DEG-18RAD-SCH80-ELL	EA
200221224ELB80	5136661	N/A	N/A	30088700028983	2"	2IN-22-1/2-DEG-24RAD-SCH80-ELL	EA
200221236ELB80	5136662	N/A	N/A	30088700028990	2"	2IN-22-1/2-DEG-36RAD-SCH80-ELL	EA
SCHEDULE 80 SPECIAL RADIUS ELBOWS — PLAIN END — SIZE 2½							
2509018ELB80	5121027	N/A	N/A	30088700013194	2½"	2-1/2-90DEG-18RAD-SCH80-ELL	EA
2509024ELB80	5121028	N/A	N/A	30088700013200	2½"	2-1/2-90DEG-24RAD-SCH80-ELL	EA
2509036ELB80	5121016	UB9FK	N/A	30088700013088	2½"	2-1/2-90DEG-36RAD-SCH80-ELL	EA
2509048ELB80	5121030	UB9HK	N/A	30088700013217	2½"	2-1/2-90DEG-48RAD-SCH80-ELL	EA
2504524ELB80	5121943	UB7DK	N/A	30088700013484	2½"	2-1/2-45DEG-24RAD-SCH80-ELL	EA
2504536ELB80	5121150	UB7FK	N/A	30088700013446	2½"	2-1/2-45DEG-36RAD-SCH80-ELL	EA
2504560ELB80	5136860	N/A	N/A	30088700947741	2½"	2-1/2-45DEG-60RAD-SCH80-ELL	EA
2503018ELB80	5121064	N/A	N/A	30088700023322	2½"	2-1/2-30DEG-18RAD-SCH80-ELL	EA
250221218ELB80	5136670	N/A	N/A	30088700029003	2½"	2-1/2-22-1/2-DEG-18RAD-SCH80-ELL	EA
250221236ELB80	5136672	N/A	N/A	30088700029010	2½"	2-1/2-22-1/2-DEG-36RAD-SCH80-ELL	EA
250221260ELB80	5123728	N/A	N/A	30088700016850	2½"	2-1/2-22-1/2-DEG-60RAD-SCH80-ELL	EA
SCHEDULE 80 SPECIAL RADIUS ELBOWS — PLAIN END — SIZE 3							
3009018ELB80	5121079	UB9DL	N/A	30088700013286	3"	3IN-90DEG-18RAD-SCH80-ELL	EA
3009024ELB80	5121020	UB9FLB	N/A	30088700013125	3"	3IN-90DEG-24RAD-SCH80-ELL	EA
3009036ELB80	5121081	UB9FLB	N/A	30088700013309	3"	3IN-90DEG-36RAD-SCH80-ELL	EA
3009048ELB80	5121082	N/A	N/A	30088700013316	3"	3IN-90DEG-48RAD-SCH80-ELL	EA
3009060ELB80	5136970	N/A	N/A	30088700029089	3"	3IN-90DEG-60RAD-SCH80-ELL	EA
3004518ELB80	5121032	UB7CL	N/A	30088700016492	3"	3IN-45DEG-18RAD-SCH80-ELL	EA
3004524ELB80	5121014	UB7DL	N/A	30088700013064	3"	3IN-45DEG-24RAD-SCH80-ELL	EA
3004536ELB80	5121077	UB7FL	N/A	30088700013262	3"	3IN-45DEG-36RAD-SCH80-ELL	EA
3004548ELB80	5121078	UB7HL	N/A	30088700013279	3"	3IN-45DEG-48RAD-SCH80-ELL	EA
3004560ELB80	5136810	N/A	N/A	30088700947727	3"	3IN-45DEG-60RAD-SCH80-ELL	EA
3003018ELB80	5136572	N/A	N/A	30088700033734	3"	3IN-30DEG-18RAD-SCH80-ELL	EA
3003024ELB80	5136573	N/A	N/A	30088700028884	3"	3IN-30DEG-24RAD-SCH80-ELL	EA
3003036ELB80	5136575	N/A	N/A	30088700018359	3"	3IN-30DEG-36RAD-SCH80-ELL	EA
300221218ELB80	5136680	N/A	N/A	30088700029027	3"	3IN-22-1/2-DEG-18RAD-SCH80-ELL	EA
300221224ELB80	5136681	N/A	N/A	30088700029034	3"	3IN-22-1/2-DEG-24RAD-SCH80-ELL	EA
300221236ELB80	5121039	N/A	N/A	30088700023315	3"	3IN-22-1/2-DEG-36RAD-SCH80-ELL	EA



90°



45°



30°



22½°