




	Part Number	Description	Light Source	Lamp Watts	Case Quantity	Example Photo	
LED EXIT SIGNS	RX3RWE	Emergency LED Exit Sign, Universal (single/double face), Red Letters, White Housing, 120/277 VAC, Damp Location Listed	LED	N/A	6		 
	RX3GWE	Emergency LED Exit Sign, Universal (single/double face), Green Letters, White Housing, 120/277 VAC, Damp Location Listed	LED	N/A	6		 
COMBINATION EXIT & EMERGENCY	CX3RW	Combination Exit and Emergency Lighting Unit, Red Letters, White Housing, Universal (single/double face), 120/277 VAC, Damp Location Listed	LED	5.4	5		 
	CX3GW	Combination Exit and Emergency Lighting Unit, Green Letters, White Housing, Universal (single/double face), 120/277 VAC, Damp Location Listed	LED	5.4	5		 
SIDE MOUNT FIXED LENS COMBINATION	FX3RW	Side Mount Fixed Lens Combination LED Exit and Emergency Lighting Unit, Red Letters, White Housing, Universal (single/double face), 120/277 VAC, Damp Location Listed	INC	5.4	5		 
	FX3GW	Side Mount Fixed Lens Combination LED Exit and Emergency Lighting Unit, Green Letters, White Housing, Universal (single/double face), 120/277 VAC, Damp Location Listed	INC	5.4	5		 
	FX3RWEC	Side Mount Fixed Lens Combination LED Exit and Emergency Lighting Unit, Red Letters, White Housing, Universal (single/double face), 120/277 VAC, Damp Location Listed, Extended Capacity to remote (2) 5.4 Watt Remote Heads	INC	5.4	5		 
	FX3GWEC	Side Mount Fixed Lens Combination LED Exit and Emergency Lighting Unit, Green Letters, White Housing, Universal (single/double face), 120/277 VAC, Damp Location Listed, Extended Capacity to remote (2) 5.4 Watt Remote Heads	INC	5.4	5		 
LOW PROFILE & 2-HEADED ADJUSTABLE	LPU	Low Profile Fixed Lens Emergency Lighting Unit, White Housing, 120/277 VAC, Damp Location Listed	INC	5.4	6		
	EM2	2-Headed Adjustable Emergency Lighting Unit, White Housing, 120/277 VAC, Damp Location Listed	INC	5.4	6		
INDOOR & OUTDOOR REMOTE HEAD	RXHSW0605	Matching Indoor Single Remote Head, 5.4 Watt Lamp, White Thermoplastic, Mounts to 3 1/2" octagon or single gang box	INC	5.4	10		
	RXHDW0605	Matching Indoor Double Remote Head, (2) 5.4 Watt Lamp, White Thermoplastic, Mounts to 3 1/2" octagon or single gang box	INC	5.4	5		
	ORHSG0605	Outdoor Sealed Single Remote Head, 5.0 Watt Lamp, Grey Thermoplastic, Mounts to 3 1/2" octagon or single gang box	INC	5.4	10		
	ORHDG0605	Outdoor Sealed Double Remote Head, (2) 5.0 Watt Lamp, Grey Thermoplastic, Mounts to 3 1/2" octagon or single gang box	INC	5.4	5		

# Remote Heads

## Matching Indoor Remote Heads



Part #: RXHDW0605



Part #: RXHSW0605

### RXHDW0605

- Double Remote Head
- Polycarbonate housing, polycarbonate lens, vacuum metalized reflector
- Includes mounting plate
- Individually boxed
- Mounts to single gang and 3½" octagon

### RXHSW0605

- Single Remote Head
- Polycarbonate housing, polycarbonate lens, vacuum metalized reflector
- Includes mounting plate
- Individually boxed
- Mounts to single gang and 3½" octagon

## Outdoor Sealed Remote Heads



Part #: ORHDG0605



Part #: ORHSG0605

### ORHDG0605

- Double Outdoor Sealed Remote Head
- PAR36 Lamp
- Grey thermoplastic housing
- Mounts to 3½" octagon

### ORHSG0605

- Single Outdoor Sealed Remote Head
- PAR36 Lamp
- Grey thermoplastic housing
- Mounts to 3½" octagon